



ECO SERIES | EF SERIES

JEWELLER | JEWELLERY INDUSTRY



PERFECT SURFACES WORLDWIDE

EXTREMELY FAST, EXTREMELY EFFICIENT

Centrifugal disc finishing machines from OTEC. The centrifugal disc finishing process is a mass finishing process specially developed for the surface treatment of work pieces.

The pieces to be finished are placed in a container in a solution of water and soap (compound) together with abrasives and usually an auxiliary agent. A rotating motion of the process container causes a relative motion between work piece and abrasive which creates a material abrasion and thus a surface finishing on the work piece.

This toroidal motion creates a very aggressive processing results which is up to 20 times more effective than conventional methods such as polishing drums. In the wet finishing process a water/compound mixture constantly flows in and out, carrying away the particles of dirt giving the work pieces a clean, corrosion-free surface finish.

The main areas of application are

- Abrasion of casting skins
- Abrasion of emery traces
- Refining of the surfaces to a hand polished quality



AREAS OF APPLICATION



Magnetic polishing

Magnetic polishing is the ideal preliminary step before wet processing. The surfaces are mechanically processed by means of tiny, rounded steel pins without causing material abrasion (important for valuable materials such as gold). The advantage of magnetic polishing is that even highly complex and delicate geometries can be processed perfectly and in the tiniest corners. With this process the surfaces achieve a beautiful shine.

The machines

ECO-Maxi magnetic: highly cost-effective

- For small and mid-sized batches
- Ideal for jewellers, goldsmiths and smaller production

MAG 30: short processing times, higher output

- For large batches
- Industrial usage for mid-sized and larger jewellery manufacturers



Wet grinding

This involves an abrasive process, in which the work pieces are finished by means of special plastic abrasives. The work pieces are moved around in a toroidal flow through the process container. Because of the different masses between the work pieces and the plastic abrasives, the material is removed and flushed out by means of the water/compound mixture. This replaces the burdensome and time consuming hand polishing and achieves very fine surfaces in as little as 3-4 hours. The patented OTEC technology represents high efficiency and unsurpassed results. Even the smallest parts can be easily processed.

The machines

ECO-mini wet: fast cleaning and grinding of jewellery

- For very small batches, prototype area
- Ideal for goldsmiths and very small production

ECO-Maxi wet: highly cost-effective

- For goldsmiths and smaller batches

EF 18/32: the newest patented technology in the gap area

- For industrial usage for jewellery manufacturers
- For maximum added value



Dry polishing

The dry polishing machines from OTEC achieve finishes as if polished by “hand”. The finest polishing granulate ensures minimal material removal in the micro-region and a brilliant shine – without damaging the set stones in the process.

The machines

ECO-mini dry: low cost with a small footprint and big in results

- For very small batches and prototype area
- Jewellers, goldsmiths, private households

ECO-Maxi dry: highly cost-effective

- For small series
- Ideal for small jewellery manufacturers, goldsmith workshops

Certified acc. to DIN 9001

This ensures optimized workflow throughout the entire production process and guarantees maximum efficiency and the highest quality assurance from engineering to production.

As a result, OTEC maintains its leadership position in the world marketplace in its efforts to create perfect surfaces.



ECO-MINI “DRY” AND “WET”

With the series ECO-mini, it has been possible to successfully integrate the technology of large, industrially used disc finishing machines into a tiny machine. The patented technology now enables the use of the finest granules with the result of a sensational shine. As if polished by hand.



Type	Container volume	Machine dimension (W x D x H)	Weight	Power consumption	Frequency
	l	mm	kg	kVA/V	Hz
ECO-mini wet	3	220 x 220 x 365	6.6	0.8 / 230	50 / 60
ECO-mini dry	3	220 x 230 x 340	3.7	0.5 / 230	50 / 60

The ECO-mini is available in two designs, “wet” and “dry”. The dry polishing machine in the mini format is predominantly used for polishing tarnished or worn jewellery or is used for the individual processing of heavy workpieces with delicate forms. The ECO-mini “wet” is predominantly used for very small batches or prototypes for the stripping of casting skins or emery traces. This makes the final polishing greatly simplified and much quicker. Thanks to the usage of plastic abrasives no orange peel appears on the jewellery pieces.

Features of the ECO-mini

It is the smallest and most efficient “finishing centre” on the market. The machine is easy to operate using a timer and works quietly without producing dust.

Areas of use

- Very small batches or prototypes
- For jewellers, jewellery retailers
- For the processing of heavier, more complex work pieces

Basic equipment of the ECO-mini wet

- Dosing pump and waste water tank
- 2.6 kg high-grade plastic abrasives
- 1 l universal compound for all metals

Basic equipment of the ECO-mini dry

- 1 kg high quality, high-grade impregnated walnut shell granulate Type H 1/100 (coarse)
- 1 kg high quality, high-grade impregnated walnut shell granulate Type H 1/500 (fine)
- 1 tube polishing paste type P 6 (110 grams)

Optional special equipment for ECO-mini dry

- Ring holder for heavy pieces of jewellery (over 7 grams)
- Processing media set for the dry processing

THE ECO-MAXI SYSTEM

The universal solution – for wet processing, dry and magnetic polishing.



With the ECO-Maxi system you have the choice to either have a so called "base unit" which incorporates all three processing procedures, or a machine for just one of the three processes. The ECO-Maxi "magnetic", the ECO-Maxi "wet" and the ECO-Maxi "dry". The modular machine concept of the ECO-Maxi is therefore perfect for smaller batch production. Due to the advanced technology, the machines are characterised by high economic efficiency with which you can save approx. 60% of your production costs.

Tree processes with just one machine: The ECO-Maxi "basic"

The ECO-Maxi basic is the drive unit without process containers. It is designed in such a way that all three processes are optimally supported. Depending on the chosen process container you can either run the magnetic polishing process, the wet grinding process or the dry polishing process – all with the same drive unit.

Basic equipment

- LC display with display of speed and process duration
- Speed control
- Bayonet fitting for the process containers
- Automatic container detection

The drive unit can be equipped with

- 1 Drive Ø 225 mm for magnetic polishing process (weight: 5 kg)
- 2 6 l process container for wet processing incl. dosing pump and waste water tank (5.5 kg)
- 3 6 l process container for dry processing (weight: 2.5 kg)



The ECO-Maxi series as single processing machines

ECO-Maxi "magnetic" (magnetic polishing)

This machine type is limited to the "magnetic polishing" process. It is the preliminary step before the wet processing and replaces the conventional electrolytic polish bath. In as little as 15–30 minutes you achieve:

- The complete removal of oxidation and imbedded mass residuals
- Shine also in delicate areas which are difficult to access

Basic equipment (not expandable)

- Timer, speed control via frequency converter, up to 1900 rpm, automatic change to the direction of rotation, 6 l process container, 200 g stainless steel pins M 4/7, 1 l compound SC 4



ECO-Maxi "wet" (wet grinding)

In this process, results are achieved in 3-4 hours which might require several days using traditional technologies. Due to the usage of special "soft" abrasives the work piece surfaces are not hardened, which reliably prevents the formation of "orange peel" on the surface. The results are:

- Complete removal of emery traces and casting skin
- Clean and light work piece surfaces

Basic equipment (not expandable)

- Timer, speed control via frequency inverter, bayonet fitting of the process container, 6 l process container for wet processing incl. dosing pump and waste water tank

Optional

- Media set for wet processing: wet processing, manual screen for "wet", 14 mm hole diameter



ECO-Maxi "dry" (dry polishing)

In this process, polishing granulates made of walnut shells provide for the finest of surfaces. Material removal in the micro-region is the result. Set diamonds, cubic zirconia or pearls will not be damaged. The processing time for the pre-polishing is about 2–3 hours and for the final polishing about 30 minutes with the following result:

- Very smooth surfaces
- Brilliant shine, comparable to hand polishing

Basic equipment (not expandable)

- Timer, speed control via frequency inverter, bayonet fitting of the process container, 6 l process container for dry processing

Optional

- Media set for dry processing: dry processing, manual screen for "dry", 4 mm hole diameter, ring holder for heavy pieces of jewellery (over 7 grams)


Eco-Maxi	"basic" (drive unit)	"dry"	"wet"	"magnetic"
Mach. dimension (WxDxH mm)	360 x 350 x 310	360 x 350 x 490	360 x 350 x 490	360 x 350 x 530
Process container volume (l; mm)	see equipment for the drive unit	6	6	Ø 225 mm
Weight (kg)	16	17	20	20
Power consumption (kVA/V)	0.8/230	0.8/230	0.8/230	0.8/230
Frequency (Hz)	50/60	50/60	50/60	50/60
Recommended workpiece quantity* (g)	–	200	300	300
Recommended fill quantity Media	–	Granulate quantity: 2.2 kg Walnut shell	Granulate quantity: 3 kg plastic abrasives or stainless steel polishing media or 4 kg porcelain polishing media	Granulate quantity: 200 g steel pins

*Depending on design, the specific and the total weight of the individual work pieces, the fill quantity for the work pieces can deviate from the recommended quantity.

EASY FINISH SERIES

The new development with the best price
to performance ratio in this category.

The EF series includes several key innovations specially customized for industrial processing of large batches. Thus an improved efficiency is achieved with a noticeably better handling capability. The EF series machines are all free standing units for wet processing. Thanks to the technical advancement of the components and a high performance capability, the EF series exhibits a price-performance ratio which was not previously achieved.



Thanks to the patented quick adjustment the container gap can be easily and quickly adjusted. From 3 mm to 0.4 mm, depending on customer requirements.

Easy Finish Series (EF 18; EF 32)

The EF series machines are high-performance and easy to operate. Newly designed containers and discs resulted in a particularly flow-friendly construction which optimizes media motion and prevents turbulence as well as creating a particularly fine grinding and polishing effect. Thus perfect, clean surfaces result without emery traces or casting skin residuals. The processing time for grinding is approx. 2-3 hours, for polishing approx. 1.5 hours. With the result:

- Very smooth surfaces
- Brilliant shine, comparable to hand polishing

Touch Panel

- Speed, chosen process time and expired process time are displayed on the new touch panel
- Parameters will be fed into the machine via touch panel only
- Advantage: Parameter adjustable for slowly end & interval function

Basic equipment EF “wet”

- Speed control via frequency inverter
- Manual screen for “wet”, 14 mm hole diameter

Optional special equipment

- Drawer system for storage of processing media
 - Integrated into the machine frame
 - For two media containers
- Cascade container
 - Fill volume 120 l
 - For waste water
- Including sludge drip basket and filter sack for filtering of accumulating dirt

The details of the EF series


The EF series contains a patented gap adjustment system. Using this technology, gap adjustments can be easily and quickly accomplished. Thus very thin jewellery pieces with a thickness of only 0.5 mm can be processed without becoming caught in the gap. That guarantees the highest process safety and processing quality.

Area of Use

- For larger batches
- For industrial usage for jewellery manufacturers



Type	Container volume	Container diameter	Machine dimension (W x D x H)	Weight	Power consumption	Frequency
	l	mm	mm	kg	kVA/V	Hz
EF 18	18	333	620 x 780 x 1.520	115	0.9/230	50 – 60
EF 32	32	400	770 x 820 x 1.520	145	0.9/230	50 – 60




Visibly better!

Form your own impression of the performance capability of our EF series machines. Simply send us a sample part that we can process in our Finishing Center. We will send you a comprehensive report, customized to your application, complete with details on the grinding and polishing media used and process parameter settings, available in 12 different languages. Naturally at no cost or obligation and absolutely confidential.


Request proof of the better technology.

TYPICAL APPLICATIONS




Example 1

- Fragmented, very thin-walled precision parts
- Machine: ECO-Maxi, Easy Finish
- Patented gap adjustment system prevents the jamming of very thin workpieces



Example 2

- Large pieces of jewellery with set-in stones
- Machine: ECO-mini, ECO-Maxi
- By using a ring holder, larger rings with stones can also be polished to a high gloss without damages.



Example 3

- Natural stones (coral, amber, etc.)
- Machine: ECO-Maxi, Easy Finish
- Through the use of special processing media and speed-optimized processing cycles delicate and breakable work pieces gently achieve a high gloss finish.



MEDIA

The processing media play an essential role in the surface quality that can be achieved. The following examples show different processing steps and the processing media which are used.



Walnut shell granulate, e.g. H 1/100, H 1/500

Impregnated walnut shell granulate is used for dry polishing. H 1/100 for pre-polishing, H/500 for fine polishing, here a high gloss is achieved which is comparable to hand polishing. Processing time approx. 2 hours in the centrifugal disc finishing process. Maximum weight of the pieces of jewellery: approx. 7-8 g. By using ring holders (or drag finishing machines series DF) dents or scratches during polishing are prevented.



Porcelain polishing media, e.g. ZSP

This is best suited for wet polishing of zinc cast and heavy silver parts. Using small porcelain pins a high gloss surface is achieved in the wet process in approx. 1.5 hours. The part on part contact of the pieces of jewellery is reduced, making this suitable heavy jewellery pieces. Example for the processing of costume jewellery, gems, pearls, amber, or brooches with porcelain media: ZSP 3/5



Plastic abrasives, e.g. KM 10, PM 10

These are particularly suited for fine, smooth surfaces. There are two shapes: K= cone shape; P= pyramid shape. Cone shape achieves very fine surfaces and is used for jewellery with stones. Pyramid shape is especially suited for the processing of corners and edges. Example of the processing of jewellery with zirconia: KM 10



Compound, e.g. SC 4, SC 5

Grinding compounds are used for the wet process and keep the workpieces clean during processing. They absorb the stripped grinding debris and ensure the continuation of the grinding effect of the abrasive. Compound examples: For wet polishing: SC 4



Polishing and grinding pastes, e.g. SP, P

Grinding or polishing pastes are only used for the dry processing. For every 5kg of granulate after 4-5 hours of processing one teaspoon of paste must be added before processing. Examples of paste applications: SP26: for fine grinding with walnut shell granulate P1: universally suited, particularly appropriate for silver P2: special for gold alloys.

You can find additional processing media in our media brochure.

WHERE WE LIVE, QUALITY HAS A LONG TRADITION



Founded in 1996, OTEC has quickly established itself as the market's technology leader by developing new machine concepts, inventions and improvements. OTEC supplies machines which are carefully tailored to the needs of specific industries and which are truly impressive in terms of cost-effectiveness, handling and precision and which are far superior to conventional systems. Around 120 members of staff are employed at the company's headquarters in Southern Germany. A global sales network ensures excellent worldwide support, and world beating finishing are always guaranteed.



CF Series



For bulk processing precision engineered workpieces.



EPAG Flex



For smoothing and polishing gold and silver workpieces.

OTEC Präzisionsfinish GmbH

Heinrich-Hertz-Str. 24 · 75334 Straubenhardt · Germany

Phone +49 7082 4911-20 · Fax +49 7082 4911-29 · E-Mail: info@otec.de

www.otec.de/en